


The manufacturer may use the mark:



Revision 2.3 November 6, 2025 Surveillance Audit Due January 1, 2026



VEL 1405020 C002

exida hereby confirms that the:

# Resilient Seated Ball Valves Velan Montreal, QC - Canada

Has been assessed per the relevant requirements of:

IEC 61508: 2010 Parts 1-2

and meets requirements providing a level of integrity to:

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2<sub>H</sub> Device

PFH/PFD<sub>avg</sub> and Architecture Constraints must be verified for each application

## Safety Function:

The Valve will move to the designed safe position per the actuator design within the specified safety time.

## Application Restrictions:

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.





Evaluating Assessor

Cho'B.

**Certifying Assessor** 

# Certificate / Certificat / Zertifikat / 合格証

VEL 1405020 C002

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2<sub>H</sub> Device

PFH/PFD<sub>avg</sub> and Architecture Constraints must be verified for each application

#### **Systematic Capability:**

The product has met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with this product must not be used at a SIL level higher than stated.

#### **Random Capability:**

The SIL limit imposed by the Architectural Constraints must be met for each element. This device meets exida criteria for Route  $2_H$ .

#### IEC 61508 Failure Rates in FIT<sup>1</sup>

Application	$\lambda_{ extsf{SD}}$	λ <sub>su</sub>	$\lambda_{ extsf{DD}}$	λ <sub>DU</sub>
Full Stroke	0	0	0	486
Tight Shut Off	0	0	0	1353
Open on Trip	0	176	0	310
Full Stroke with PVST	0	0	174	312
Tight Shut Off with PVST	0	0	174	1179
Open on Trip with PVST	176	0	174	136

<sup>&</sup>lt;sup>1</sup> FIT = 1 failure / 10<sup>9</sup> hours

PVST = Partial Valve Stroke Test of a final element Device

#### SIL Verification:

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH/PFD<sub>avg</sub> considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each element must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

Assessment Report: VEL 14-05-020 Velan Assessment Report R003 V2R3

Safety Valves IEC 61508 Assessment (or later)

Safety Manual: SIL-BV



**Resilient Seated Ball** 

**Valves** 

80 N Main St Sellersville, PA 18960