

The manufacturer may use the mark:



Revision 2.3 November 6, 2025 Surveillance Audit Due January 1, 2026

Certificate / Certificat Zertifikat / 合格証

VEL 1405020 C003

exida hereby confirms that the:

Metal Seated Ball Valves Velan Montreal, QC - Canada

Has been assessed per the relevant requirements of:

IEC 61508: 2010 Parts 1-2

and meets requirements providing a level of integrity to:

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2_H Device

PFH/PFD_{avg} and Architecture Constraints must be verified for each application

Safety Function:

The Valve will move to the designed safe position per the actuator design within the specified safety time.

Application Restrictions:

The unit must be properly designed into a Safety Instrumented Function per the Safety Manual requirements.





Evaluating Assessor

Cho'B.

hiteys IR

Certifying Assessor

Certificate / Certificat / Zertifikat / 合格証

VEL 1405020 C003

Systematic Capability: SC 3 (SIL 3 Capable)

Random Capability: Type A, Route 2_H Device

PFH/PFD_{avg} and Architecture Constraints must be verified for each application

Systematic Capability:

The product has met manufacturer design process requirements of Safety Integrity Level (SIL) 3. These are intended to achieve sufficient integrity against systematic errors of design by the manufacturer.

A Safety Instrumented Function (SIF) designed with this product must not be used at a SIL level higher than stated.

Random Capability:

The SIL limit imposed by the Architectural Constraints must be met for each element. This device meets exida criteria for Route 2_H .

IEC 61508 Failure Rates in FIT¹, Securaseal Top-Entry Clean Service

Application	$\lambda_{ extsf{SD}}$	$\lambda_{ extsf{SU}}$	$\lambda_{ extsf{DD}}$	λ _{DU}
Full Stroke	0	0	0	477
Tight Shut Off	0	0	0	1343
Open on Trip	0	176	0	301
Full Stroke with PVST	0	0	169	308
Tight Shut Off with PVST	0	0	169	1174
Open on Trip with PVST	176	0	169	132

¹ FIT = 1 failure / 10⁹ hours

PVST = Partial Valve Stroke Test of a final element Device

SIL Verification:

The Safety Integrity Level (SIL) of an entire Safety Instrumented Function (SIF) must be verified via a calculation of PFH/PFD_{avg} considering redundant architectures, proof test interval, proof test effectiveness, any automatic diagnostics, average repair time and the specific failure rates of all products included in the SIF. Each element must be checked to assure compliance with minimum hardware fault tolerance (HFT) requirements.

The following documents are a mandatory part of certification:

Assessment Report: VEL 14-05-020 Velan Assessment Report R003 V2R3

Safety Valves IEC 61508 Assessment (or later)

Safety Manual: SIL-MS



Metal Seated Ball

Valves

80 N Main St Sellersville, PA 18960